

Repair under control

Hot Air Stations


Offer complete control of the rework process by using temperature and air flow profiles. Obtain the maximum quality when soldering.

Precision Hot Air Station


To repair small and medium SMDs quickly and safely.

Control the temperature and the air flow by using profiles

These new stations features along with the manual mode a powerful functionality of profiles to perform rework tasks with the maximum precision.



The operator can set the temperature values and air flow rate manually depending on the task.



You can control temperature values and air flow rate by creating up to 25 profiles.

Hot Air Station

High-powered stations for repairing all kinds of SMD components.



Control thermocouple

Ref. PH218

Read the temperature at a specific point on the PCB. It allows precise control of the temperature applied to the solder joint (regardless of the distance between the heater and the PCB or the component). It can also be used as a protection sensor.







Auto-stop function

Hot Air Stands Ref. JT-SD & TE-SD

Safer and more efficient

The auto-stop function is a safety measure which guarantees the heat is automatically cut off when the tool is in the stand. This also means you save power and extend the life of the tip.

Pedal

When you select this function the tool will only heat up when the pedal is pressed.



Desoldering in 3 simple steps

Extractor Desk

Ref. 0008752

By using the wide range of extractors & protectors, you can desolder quickly and at the same time protect the surrounding components by concentrating the heat on the selected component.

1. Placing

Choose the extractor, tripod or protector which best fits the component.



2. Heating


While you apply the heat

to the component, the surrounding elements are protected.



3. Extracting

Automatic withdrawal of the desoldered component.



Communications

The Hot Air stations have different connectors so data is shared with other equipment. Widen your range of tasks!



Auxiliary connection

USB-B Port

First JBC Hot Air stations that allow control from PC via USB. You can import and export profiles and easily apply them to other stations. You can also manage the stations using a Robotic system thanks to a Robot Communication Protocol.



ROBOT connector

Connector RJ-12 for RS 232 connection using a protocol for robots. This option requires an external robotic connection where the robot manages the JBC control unit.

Specifications

	JTSE	JTSE-Q	TESE	TESE-Q
Dimensions (control unit)	148 x 184 x 140 mm	(5.83 x 7.24 x 5,51 in)	148 x 184 x 140 mm	(5.83 x 7.24 x 5,51 in)
Weight	5.7 Kg (12.6 lb)	5.7 Kg (12.6 lb)	5.4 Kg (11.9 lb)	5.4 Kg (11.9 lb)
Ref Voltage (AC) - Fuse	,	60Hz - 8A. Rated current: 7A Hz - 4A. Rated current: 3A		60Hz - 8A. Rated current: 7A Hz - 4A. Rated current: 3A
Nominal Power	70	OW	30	WOO
Temperature selection	Room Temp. / 150 -	450 °C (300 - 840 °F)	Room Temp. / 150 -	450 °C (300 - 840 °F)
Cool mode	T off. Used to blow a	ir to room temperature	T off. Used to blow a	ir to room temperature
Ambient operating temp.	10 - 40 °C	(50- 104°C)	10 - 40 °C	(50- 104°C)
Air flow regulator	5 - 50	SLPM	3 - 17	'SLPM
Vacuum	30% / 228 n	nmHg (9 inHg)	30% / 228 n	nmHg (9 inHg)
Temperature measurement	Thermoco	uple type K	Thermoco	uple type K
Extractor desk (Ref. 0008752)	~	-	~	-



Accessories

Choose the model to suit your needs

Heater set



Ref. JT-TA



Nozzles TE

	Ref.	Größe (mm)	Größe (in)
Bent	TN9787	Ø3	Ø 0.12
11	TN9785	Ø 4	Ø 0.16
	TN9782	Ø 5	Ø 0.2
Bent 45°	TN8851	ØЗ	Ø 0.12
	TN8905	Ø 4	Ø 0.16
	TN9561	Ø 5	Ø 0.2
Straight	TN9209*	Ø3	Ø 0.12
17	TN9208*	Ø 4	Ø 0.16
8	TN9080*	Ø 5	Ø 0.20

Nozzles JT

	Ref.	Größe (mm)	Größe (in)
Bent	JN2015 *	Ø 4	Ø 0.16
1	JN2012*	Ø 6	Ø 0.24
	JN6633	Ø8	Ø 0.31
Straight	JN2020*	Ø 8	Ø 0.31
	JN8417	Ø 10	Ø 0.4
Flat	JN7637	10 x 2	0.4 × 0.08
20	JN7638	20 x 2	0.8 × 0.08
	JN7639	30 x 2	1.18 x 0.08

*Supplied with JTSE / TESE

Protectors

		Ref.	Größe AxB (mm)	Größe AxB (in)
		P3353	4,3 x 3	0.16 x 0.12
		P3786	5,2 x 5,2	0.20 x 0.20
		P3352	5,2 x 7,5	0.20 x 0.29
TRIPOL		P3355	5,2 x 9,5	0.20 x 0.37
		P3356	6,2 x 4,2	0.24 x 0.16
	— TRIPOD	P3785	7,2 x 7,2	0.28 x 0.28
	ROTECTOR	P3784	8,2 x 8,2	0.32 x 0.32
1.8.		P4035	9 x 13	0.35 x 0.51
	>_	P4040	9,5 x 19	0.7 x 0.74
~~~~~		P4080	9,5 x 21	0.7 x 0.83

Ref.	Größe AxB (mm)	Größe AxB (in)
P2220 *	10 x 10	0.39 x 0.39
P4045	10,5 x 21	0.14 x 0.82
P4090	11 x 16	0.43 x 0.63
P2235 *	12 x 17	0.47 x 0.67
P1249	12 x 23	0.47 x 0.9
P4000*	12,5 x 12,5	0.49 x 0.49
P1593	13 x 31,5	0.51 x 1.24
P3354	13,2 x 13,2	0.52 x 0.52
P4025	13,5 x 21,5	0.53 x 0.85
P2230 *	15 x 15	0.59 x 0.59

*Supplied with JTSE / TESE

Ref.	Größe AxB (mm)	Größe AxB (in)
P4010*	17 x 17	0.67 × 0.67
P4005	18 x 29	0.71 x 1.14
P4030	18,5 x 18,5	0.73 × 0.73
P1068	18,5 x 24	0.73 x 0.94
P2685	28,5 x 28,5	1.12 x 1.12
P4085	31,5 x 31,5	1.24 x 1.24
P2672	33 x 46	1.30 x 1.18
P4002	50 x 50	1.97 x 1.97
P3357	52,5 x 14	2.06 x 0.55

 * Supplied with JTSE / TESE

## Extractors

Ref.	Größe (mm)	Größe (in)
E2052 *	20 x 20	0.79 x 0.79
E2064*	20 x 26	0.79 x 1.02
E2184 *	24 x 24	0.94 x 0.94
E2068	27 x 27	1.06 x 1.06
E4020	28,5 x 28,5	1.12 x 1.12
E4015	31,5 x 31,5	1.24 x 1.24
E2084	33 x 33	1.30 x 1.30
E2100	38 x 38	1.50 x 1.50
E2124	45 x 45	1.77 x 1.77
	E2052 * E2064 * E2184 * E2068 E4020 E4015 E2084 E2100	E2052 *       20 x 20         E2064 *       20 x 26         E2184 *       24 x 24         E2068       27 x 27         E4020       28,5 x 28,5         E4015       31,5 x 31,5         E2084       33 x 33         E2100       38 x 38

*Supplied with JTSE / TESE

## Tripods

Ref.	Größe (mm)	Größe (in)	
T2050 *	Ø 39	Ø 1.53	
T2250 *	Ø 85	Ø 3.35	

## Manual extractor

Ref.	Größe (mm)	Größe (in)
E2190	Ø7	Ø 0.27


**Extractor Desk** Ref. 0008752

Protectors and extractors not included

## RW Rework Arm

The Rework Arm for Hot Air stations

- ➤ It supports the Hot Air heater and leaves the operator free
- ➤ It allows full access to the whole work area
- ➤ The arm's vertical movement adapts to all your needs



## Vertical movement

Thanks to the multiple arm joints the height of the arm can be adjusted to suit all components whatever their size.







## Articulated arm

It facilitates access to the work area by holding the arm in place once the knobs have been tightened.



The Ball joint allows you to adjust the tool head holder position.



Ball joint



Once the arm has been positioned select the Hot Air stations profiles: - temperature

- air flow
- time

Fix the tool in place when you need to repeat the operation for the same batch of PCBs.



## Specifications

# RWB-B RWS-B RWT-B Height 386,5 mm (15.22 in) 386,5 mm (15.22 in) 386,5 mm (15.22 in) Base 480 x 550 mm (18.90 x 21.65 in) 270 x 400 mm (10.63 x 15.75 in) 444,5 mm (17.5 in) Arm lenght 444,5 mm (17.5 in) 444,5 mm (17.5 in) 444,5 mm (17.5 in)

## Swivel clamp

This keeps the hose away from the work area to keep it free of obstacles.



## Preheaters for PCBs

Obtain maximum quality in soldering without thermal stress. The complete answer to pre-heating PCBs. There are two independent heating areas with uniform heat distribution.

#### Infrared Preheater set

Ref. PHSE-1KA 120 V, PHSE-2KA 230 V, PHSE-9KA 100 V

This is the best way to preheating small PCBs.

#### Convection Preheater set

Ref. PHBE-1KA 120 V, PHBE-2KA 230 V, PHBE-9KA 100 V

Essential for soldering in multilayered circuits.



## Comparison between Preheaters Technical specifications

·		
	PHSE-B	PHBE-A
Heating area	65 x 135 mm (2.56 x 5.31 in) - 1 zone 130 x 135 mm (5.12 x 5.31 in) - 2 zones	180 x 277 mm (7.09 x 10.9 in) - 1 zone 360 x 277 mm (14.17 x 10.9 in) - 2 zones
Voltage – maximum power	PHS-1B 120V, 50 / 60Hz - 500 VA PHS-2B 230V, 50 / 60Hz - 500 VA PHS-9B 100V, 50 / 60Hz - 500 VA	PHB-1A 120V, 50 / 60Hz - 1800 VA PHB-2A 230V, 50 / 60Hz - 2000 VA PHB-9A 100V, 50 / 60Hz - 1500 VA
Heating system	Infrared	Convection
Temperature range	50 - 250 °C (120 - 482 °F)	50 - 250 °C (120 - 482 °F)
Maximum work time	600 min. o indefinite	600 min. o indefinite
JBC set temperature profiles	3 profiles (2, 3 or 4 steps)	3 profiles (2, 3 or 4 steps)
Operator's temperature profiles	up to 25 (6 steps per profile)	up to 25 (6 steps per profile)
Temperature measurement	Thermocouple type K (x4)	Thermocouple type K (x4)
Dimensions	173 x 282 x 41 mm (6.81 x 11.1 x 1.61 in)	404 x 440 x 41 mm (15.9 x 17.32 x 1.61 in)
Weight	2,9 kg (6.4 lb)	7,2 kg (15,9 lb)





